



Head Office & Customer Service

McKay Avenue PO Box 373
LEETON NSW 2705 LEETON NSW 2705
Phone: (02) 6953 7677 Fax: (02) 6953 6266
Email: inquiries@malmet-aus.com.au

ABN 95 001 717 791

A.B.N. 98 078 566 604

Trading as **EVO CARE** and **L&M EQUIPMENT**

P.O. Box 1144, Stafford Qld. 4053

Ph: 07 3355 8000 Fax: 07 3355 5043

Website: <http://www.evocare.com.au>

E-Mail: sales@evocare.com.au

workshop@evocare.com.au



Quality

ISO 9001

Drying Cabinet DCA / DC1-2



Spare Parts Catalogue

*'Due to Malmet's policy of continuous product improvement, information
in this document may change without notice.'*

Table of Contents

<i>Contents</i>	<i>Page</i>
<i>Electrical</i>	<i>3</i>
<i>PCB / Harness</i>	<i>3</i>
<i>Control Panel.....</i>	<i>3</i>
<i>Individual Componentry.....</i>	<i>3</i>
<i>Door.....</i>	<i>4</i>
<i>Cabinet Assembly.....</i>	<i>4</i>
<i>Fan Assembly.....</i>	<i>4</i>
<i>Miscellaneous</i>	<i>4</i>
<i>Manufactured Materials / Spare Parts</i>	<i>4</i>

In the interest of continued product improvement, MALMET (AUSTRALIA) reserves the right to alter specifications without notice. E. & O. E.

Text and illustration © Copyright MALMET (AUSTRALIA) 2008

All rights reserved. No part of this document may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying, recording or by an information storage and retrieval system, without prior permission in writing from Malmnet (Australia).



Spare Parts Catalogue

Electrical

1	Element FH21 1500W	8-2005SP	DCA/DC1-2	2	
2	Thermostat T1603	8-2001SP	DCA/DC1-2	1	
3	Plug 3 Pin 15 Amp Clear	8-2057SP	DCA/DC1-2	1	
4	Microswitch HO.BZ-2RW	8-2038SP	DCA/DC1-2	1	
5	TF1603 Cut Out Thermostat Complete	822-2055SP	DCA/DC1-2	1	
6	Temperature Probe (950mm Long)	81-2405SP	DC1-2	1	
7	Contactorm GMC-9-11-U	1-20-620SP	DC1-2	1	
8	Thermocouple Probe 'K'	8-2043SP	DCA	1	
9	TL80 Transformer White (Power On)	82-2697SP	DCA	1	No longer available
10	TL80 Transformer Amber (In Progress)	82-2689SP	DCA	1	
11	RKC4 Controller (without Capacitor)	8-M00-87-181SP	DCA	1	

PCB / Harness

12	Relay LY-2 240V AC	82-2125SP	DCA	1	
13	Relay PCB Board Modified	87-5050SP	DC1-2	1	After August 2001
14	Harness 10 Way Connecting	87-5052SP	DC1-2	1	After August 2001
15	Circuit Board Pillar (Stand Off)	81-2308SP	DC1-2	4	

Control Panel

16	Front Panel with Display Board	8-K00-87-006SP	DC1-2	1	
17	Front Panel with Overlay	8-K00-87-005SP		1	
18	Display Board DC	87-5051SP		1	
19	Front Panel Plastic	8-M00-84-0019SP		1	
20	Display Overlay DC	87-2241SP		1	

Individual Componentry

21	Seal Rubber	8-M00-84-0037SP	DC1-2	1	
22	Anodised Label Moist Air Bleed Off	8-4143SP	DC1-2	1	
23	Control Panel Stand Off	8-M00-83-0608SP	DC1-2	3	



Spare Parts Catalogue

Door

24	Doors Glass DC1-2	87-5000SP	DC1-2	1 set	DC2 (2 Sets)
25	Latch Flush Cup	8-8011SP	DC1-2	1	
26	Hinge Assembly DC	8-M00-87-125SP	DC1-2	2	
27	Magnetic Door Latch Conversion	8-K00-87-007SP	DC1-2	1	
28	Magnetic Door Latch	87-5006SP	DC1-2	1	

Cabinet Assembly

29	Door Gasket Assembly (S/S Doors) 5.5mt	8-M00-87-140SP	DC1-2	1	Z Profile
30	Door Gasket Assembly (Glass Doors) 7.5mt	8-M00-87-145SP	DC1-2	2	
31	Air Prefilter Foam 150mm x 150mm	8-M00-87-115SP	DCA/DC1-2	1	
32	Insertion Rubber 3mm (10 Holes)	8-M00-87-110SP	DCA/DC1-2	2	
33	Insertion Rubber 1.6mm x 1.2mt (16 Holes)	8-M00-87-105SP	DCA/DC1-2	2	
34	Insertion Rubber (18 Holes)	8-M00-87-111SP	DC1-2	2	
35	Door Seal Gasket (Pre-moulded 2001)	87-5015SP	DC1-2	2	

Fan Assembly

36	Fan 270 dia. X 125.5 Wide	8-K00-87-001SP	DC1-2	1	
37	Fan Boss (Heat Ring)	8-M00-87-096SP	DC1-2	1	
38	Motor 809416 NTE-C01	86-1011SP	DCA/DC1-2	1	
39	Rubber Mount M141	81-4291SP	DCA/DC1-2	4	

Miscellaneous

40	Adjustable Foot and Insert	82-8095SP	DC1-2	4	2004 onwards
41	On/Off Toggle Switch	8-2027SP	DCA	1	
42	TL80 Globes (6 Volt)	82-2531SP	DCA	1	
43	Spring Compression C612 (Reset)	8-4218SP	DCA	1	

Manufactured Material / Spare Parts

44	Instrument Tray DC (362 x 271 x 22mm)	8-M00-87-033SP	DC1-2	2	
45	Basket DC (279 x 108 x 77mm)	8-M00-87-150SP	DC1-2	2	
46	Air Diffuser Blank	8-M00-87-034SP	DC1	3	
	Air Diffuser Blank	8-M00-87-034SP	DC2	1	
47	Air Diffuser	8-M00-87-035SP	DC1	3	
	Air Diffuser	8-M00-87-035SP	DC2	1	
48	½ Width Shelf	87-0215SP	DC		
49	Full Width Shelf	87-0139SP	DC		
50	Tube Holder Complete (10 Tubes)	8-M00-87-095SP	DCA	2	
51	Tube Holder Complete (16 Tubes)	8-M00-87-100SP	DCA	2	
52	Tube Holder Complete (18 Tubes)	8-M00-87-104SP	DC1-2	2	
53	Anaesthetic Bag Holders D/Sided 6	8-M00-87-038SP	DCA	1	